



TUV T8

TUV 55W HO 6PK

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury.
- $\boldsymbol{\cdot}$ Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Lamp Current (Nom)	0.765 A
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Voltage (Nom)	86 V
Useful Life (Nom)	9,000 hour(s)	Voltage (Nom)	86 V
Light Technical		Mechanical and Housing	
Color Code	TUV	Bulb Shape	T26 [T 26mm]
Color Designation	- [Not Specified]		
Depreciation at Useful Lifetime	15 %	Approval and Application	
		Mercury (Hg) Content (Nom)	2.0 mg
Operating and Electrical			
Power Consumption	54 W		


TUV T8

UV			
UV-C Radiation at 100 hr	19.7 W		
Product Data			
Order product name	TUV 55W HO 1SL/6		
Full product name	TUV 55W HO 6PK		
Full product code	871150061866510		
Order code	376343		


Material Nr. (12NC)	928049504003		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8711500618665		
Numerator - Packs per outer box	6		
EAN/UPC - Case	8711500618672		

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 55W HO 1SL/6	1-1/8 inch	35-1/4 inch	35-1/2 inch	35-7/16 inch	35-13/16 inch



Photometric data



Spectral Power Distribution Colour - TUV 55W HO 1SL/6



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 19 - data subject to change