



MasterColor CDM-R Elite

MASTERColor CDM-R Elite 35W/930 E26/24 PAR20 10D

The Elite family is at the very top of the MasterColor CDM range, and gives a unique combination of unbeatable light quality and consistent performance over lifetime, while keeping running costs low. MasterColor metal halide lamps deliver consistent white light and higher color rendering than any standard metal halide source for architectural lighting. MasterColor CDM Elite PAR30L lamps deliver similar performance as the MasterColor Elite family lamps in the familiar PAR30L shape.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Life to 5% Failures (Nom)	9000 h
Life To 10% Failures (Nom)	10000 h
Life to 20% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
ANSI Code HID	C130/E
Switching Cycle	1350X
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	10 °
Beam Angle Technical (Nom)	12 °
Luminous Intensity (Nom)	26000 cd
Beam Description	Spot
Color Designation	Warm White (WW)

Lumen Maintenance 12000 h (Nom)	82 %
Lumen Maintenance 2000 h (Nom)	94 %
Lumen Maintenance 4000 h (Nom)	90 %
Design Mean Lumens	2040 lm
Chromaticity Coordinate X (Nom)	0.437
Chromaticity Coordinate Y (Nom)	0.400
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	61 lm/W
Color Rendering Index (Min)	88
Color Rendering Index (Nom)	91
LLMF At End Of Nominal Lifetime (Nom)	80 %
Luminous Flux in 90° Cone (Rated)	2100 lm
Operating and Electrical	
Power (Rated) (Nom)	39.0 W
Ignition Supply Voltage (Min)	198 V
Re-Ignition Time (Min) (Max)	15 min

MasterColor CDM-R Elite

Warm Up Time to 60% Light (Nom)	120 s
Ignition Time (Max)	30 s
Voltage (Max)	96 V
Voltage (Min)	80 V
Voltage (Nom)	88 V

Controls and Dimming

Dimmable	No
Run-Up Time 90% (Max)	3 min

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Approval and Application

Energy Efficiency Label (EEL)	Not applicable
Mercury (Hg) Content (Nom)	4.7 mg
Energy Consumption kWh/1000 h	43 kWh

Luminaire Design Requirements

Bulb Temperature (Max)	300 °C
Cap-Base Temperature (Max)	200 °C

Product Data

Order product name	MASTERColor CDM-R Elite 35W/930 E26 PAR20 10D
EAN/UPC - Product	046677434182
Order code	434183
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928050000615
Net Weight (Piece)	0.112 kg

Warnings and Safety


Dimensional drawing

D


Product	D (max)	C (max)
MASTERColor CDM-R Elite 35W/930 E26 PAR20 10D	65 mm	95 mm

CDM-R Elite 35W/930 E26 PAR20 10D

Photometric data



LDLD_CDM-R-E_0015-Light distribution diagram



MasterColor CDM-R Elite

Lifetime

