



HPL-N

HPL-N 80W/542 E27 SG 1CT/24

標準型高壓水銀燈

安全提示

- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般資訊	
燈座基底	E27 [E27]
操作位置	UNIVERSAL [任何或通用 (U)]
壽命 (故障率 50%) (標稱)	16,000 h
照明技術	
色碼	542 [CCT of 4200K]
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	370
色度坐標 Y (Nom)	366
相關色彩溫度 (規範)	4200 K
光效 (額定) (標準)	44.5 lm/W
演色性指數 (CRI)	45
運轉與電力	
耗電量	80.0 W
電壓 (標稱)	115 V
電壓 (標稱)	115 V

控制與調光	
可調光	否
機械與外罩	
燈泡表層	塗層玻璃
燈泡材質	軟玻璃
燈泡形狀	BF70 [BF 70mm]
認證與應用	
汞 (Hg) 含量 (標稱)	14.0 mg
能源消耗 kWh/1000 h	88 kWh
產品資料	
下訂產品名稱	HPL-N 80W/542 E27 SG 1CT/24
完整產品名稱	HPL-N 80W/542 E27 SG 1CT/24
完整產品代碼	871150017997599
訂單代碼	928051007396
材質 Nr. (12NC)	928051007396
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500179975

HPL-N


分子 - 每一外盒包裝	24
EAN/UPC - 箱	8711500179982

二维绘图




Product	D (max)	C (max)
HPL-N 80W/542 E27 SG 1CT/24	71 mm	155 mm

光度数据




Spectral Power Distribution Colour - HPL-N 80W/542 E27 SG 1CT/24

壽命



Life Expectancy Diagram - HPL-N 80W/542 E27 SG 1CT/24



Lumen Maintenance Diagram - HPL-N 80W/542 E27 SG 1CT/24

