



MASTER MHN-LA

MASTER MHN-LA 1000W/956 230V XWH

Compact quartz metal halide lamps with double-pinch

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- · Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information				
Cap-Base	X528			
Operating Position	P5 [Parallel +/-5D or Horizontal(HOR)]			
Life to 50% Failures (Nom)	15,000 hour(s)			
Light Technical				
Color Code	956 [CCT of 5600K]			
Color Designation	Daylight			
Chromaticity Coordinate X (Nom)	337			
Chromaticity Coordinate Y (Nom)	331			
Correlated Color Temperature (Nom)	5600 K			
Luminous Efficacy (rated) (Nom)	86.0 lm/W			
Color rendering index (CRI)	80			
·	·			

Arc Length O (Nom)	40.5 mm	
Operating and Electrical		
Power Consumption	1,040.0 W	
Voltage (Nom)	125 V	
Voltage (Nom)	125 V	
Controls and Dimming		
Dimmable	No	
Mechanical and Housing		
Bulb Finish	Clear	
Bulb Shape	TD40	
·	·	


Datasheet, 2023, April 14 data subject to change

MASTER MHN-LA

Approval and Application			
Mercury (Hg) Content (Nom)	95 mg		
Energy Consumption kWh/1000 h	1144 kWh		
Product Data			
Order product name	MASTER MHN-LA 1000W/956 230V XWH		
Full product name	MASTER MHN-LA 1000W/956 230V XWH		
Full product code	871150020077800		


Order code	928072205130
Material Nr. (12NC)	928072205130
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291548218
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500200778

Dimensional drawing



Product	D (max)	0	Χ	Α
MASTER MHN-LA 1000W/956 230V XWH	40 mm	40.5 mm	35 mm	286 mm


Photometric data




Spectral Power Distribution Colour - MASTER MHN-LA 1000W/956 230V XWH

MASTER MHN-LA

Lifetime





Life Expectancy Diagram - MASTER MHN-LA 1000W/956 230V XWH

Lumen Maintenance Diagram - MASTER MHN-LA 1000W/956 230V XWH



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.