



HPI-T 複金屬燈

HPI-T 2000W/542 E40 380V 1SL/4

石英複金屬燈，透明外部燈泡

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	E40
操作位置	P20 [平行 +/-20D 或水平 (HOR)]
壽命 (故障率 50%) (標稱)	12,000 h
照明技術	
色碼	542 [CCT of 4200K]
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	387
色度坐標 Y (Nom)	403
相關色彩溫度 (規範)	3800 K
光效 (額定) (標準)	101 lm/W
演色性指數 (CRI)	59
電弧長 O (標稱)	120 mm
運轉與電力	
耗電量	1,980 W
電壓 (標稱)	232 V


電壓 (標稱)	232 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	T100
認證與應用	
汞 (Hg) 含量 (標稱)	256 mg
能源消耗 kWh/1000 h	2178 kWh
產品資料	
下訂產品名稱	HPI-T 2000W/542 E40 380V 1SL/4
完整產品名稱	HPI-T 2000W/542 E40 380V 1SL/4
完整產品代碼	871150020235245
訂單代碼	928074209228

HPI-T 複金屬燈

材質 Nr. (12NC)	928074209228
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500202352
分子 - 每一外盒包裝	4


EAN/UPC - 箱	8711500202369
-------------	---------------

二维绘图




Product	D (max)	O	L	C (max)
HPI-T 2000W/542 E40 380V 1SL/4	101.5 mm	120 mm	267 mm	430 mm

光度数据



Spectral Power Distribution Colour - HPI-T 2000W/542 E40 380V 1SL/4

壽命



Life Expectancy Diagram - HPI-T 2000W/542 E40 380V 1SL/4

Lumen Maintenance Diagram - HPI-T 2000W/542 E40 380V 1SL/4

HPI-T 複金屬燈

