

Lighting

PHILIPS

MHN-TD

MHN-TD 150W/842 RX7s 1CT/12

Double-envelope, single- or double-ended Metal halide lamps

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- \cdot The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical		
Cap-Base	RX7s	Power Consumption	155.0 W	
Operating Position	P45 [Parallel +/-45D or Horizontal(HOR)]	Voltage (Nom)	98 V	
Flux measurement reference	Sphere	Voltage (Nom)	98 V	
Life to 50% Failures (Nom)	10,500 h			
		Controls and Dimming		
Light Technical		Dimmable	No	
Color Code	842 [CCT of 4200K]			
Luminous Flux	12,500 lm	Mechanical and Housing		
Color Designation	Cool White (CW)	Bulb Finish	Clear	
Chromaticity Coordinate X (Nom)	0.371	Bulb Shape	TD	
Chromaticity Coordinate Y (Nom)	0.366			
Correlated Color Temperature (Nom)	4200 K	Approval and Application		
Luminous Efficacy (Rated) (Min)	73 lm/W	Energy Efficiency Class	G	
Luminous Efficacy (rated) (Nom)	81 lm/W	Mercury (Hg) Content (Max)	12.3 mg	
Color rendering index (CRI)	81	Mercury (Hg) Content (Nom)	12.3 mg	
Arc Length O (Nom)	17.8 mm	Energy Consumption kWh/1000 h	155 kWh	

MHN-TD

EPREL Registration Number	473320		
Product Data			
Order product name	MHN-TD 150W/842 RX7s 1CT/12		
Full product name	MHN-TD 150W/842 RX7s 1CT/12		
Full product code	871829121536300		
Local code description	MHNTD150W842		
Order code	928076505190		


Material Nr. (12NC)	928076505190		
Local order code	MHNTD150W842		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8718291215363		
Numerator - Packs per outer box	12		
EAN/UPC - Case	8718291215370		

Dimensional drawing




Product	D (max)	D	0	C (max)
MHN-TD 150W/842 RX7s 1CT/12	23.0 mm	0.89 inch	17.8 mm	135.4 mm

Photometric data




Light Distribution Diagram - MHN-TD 150W/842 RX7s 1CT/12



Spectral Power Distribution Colour - MHN-TD 150W/842 RX7s 1CT/12

MHN-TD

Lifetime



Life Expectancy Diagram - MHN-TD 150W/842 RX7s 1CT/12

Lumen Maintenance Diagram - MHN-TD 150W/842 RX7s 1CT/12



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 14 - data subject to change