



MSR

MSR 1200 1CT/3

MSR – bright vivid colours, always The high colour rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colours of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | Arc Length O (Nom) | |
|------------------------------------|----------------------------------|--------------------------|-----------------|
| Cap-Base | G22 [G22] | 10.0 mm | |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Operating and Electrical | |
| Life to 50% Failures (Nom) | 800 hour(s) | Power Consumption | 1,200 W |
| | | Lamp Current (Nom) | 13.8 A |
| Light Technical | | Controls and Dimming | |
| Color Code | - [Not Specified] | Dimmable | No |
| Luminous Flux | 103,000 lm | Product Data | |
| Chromaticity Coordinate X (Nom) | 325 | Order product name | MSR 1200 1CT/3 |
| Chromaticity Coordinate Y (Nom) | 327 | Full product name | MSR 1200 1CT/3 |
| Correlated Color Temperature (Nom) | 5900 K | Full product code | 872790091121300 |
| Luminous Efficacy (rated) (Nom) | 88 lm/W | Order code | 928078105114 |
| Color rendering index (CRI) | 80 | | |

MSR

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 928078105114 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900911213 |
| Numerator - Packs per outer box | 3 |


| | |
|----------------|---------------|
| EAN/UPC - Case | 8727900911220 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F |
|----------------|---------|---------|---------|---------|-------|---------|-------|
| MSR 1200 1CT/3 | 40 mm | 10.0 mm | 84 mm | 86 mm | 85 mm | 175 mm | 53 mm |

Photometric data



Spectral Power Distribution Colour - MSR 1200 1CT/3

