



MASTER MHN-SA

MASTER MHN-SA 1800W/956 (P)SFC 400V

Compact quartz metal halide lamps with double-pinch

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Arc Length O (Nom)	
Cap-Base	(P)SFC [(P)SFC]	25 mm	
Operating Position	P15 [Parallel +/-15D or Horizontal(HOR)]		
Life to 50% Failures (Nom)	6,100 hour(s)		
Light Technical		Operating and Electrical	
Color Code	956 [CCT of 5600K]	Power Consumption	1,850.0 W
Color Designation	Daylight	Voltage (Nom)	205 V
Chromaticity Coordinate X (Nom)	330	Voltage (Nom)	205 V
Chromaticity Coordinate Y (Nom)	339		
Correlated Color Temperature (Nom)	5600 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	86 lm/W	Dimmable	No
Color rendering index (CRI)	86	Mechanical and Housing	
		Bulb Finish	Clear
		Bulb Shape	TD40 [TD 40mm]

MASTER MHN-SA

Approval and Application	
Mercury (Hg) Content (Nom)	234 mg
Energy Consumption kWh/1000 h	2035 kWh
Product Data	
Order product name	MASTER MHN-SA 1800W/956 (P)SFC 400V
Full product name	MASTER MHN-SA 1800W/956 (P)SFC 400V
Full product code	871150020076100


Order code	928079315130
Material Nr. (12NC)	928079315130
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291548270
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500200761

Dimensional drawing



Product	D (max)	O	C (max)
MASTER MHN-SA 1800W/956 (P)SFC 400V	41 mm	25 mm	364 mm


Photometric data




Spectral Power Distribution Colour - MASTER MHN-SA 1800W/956 (P)SFC 400V

MASTER MHN-SA

Lifetime



Life Expectancy Diagram - MASTER MHN-SA 1800W/956 (P)SFC 400V



Lumen Maintenance Diagram - MASTER MHN-SA 1800W/956 (P)SFC 400V

