



CDM-TD 陶瓷放電管複金屬燈泡

MASTERC CDM-TD 70W/830 RX7s 1CT/12

精巧、高效率雙端型放電燈，光色歷久如新，光線清晰明亮

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	RX7s
操作位置	P45 [平行 +/-45D 或水平 (HOR)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	16,000 h
照明技術	
色碼	830 [CCT of 3000K]
光通量	6,000 lm
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.434
色度坐標 Y (Nom)	0.398
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	85 lm/W
演色性指數 (CRI)	80


電弧長 Ø (標稱)	8 mm
運轉與電力	
耗電量	71.0 W
電壓 (標稱)	94 V
電壓 (標稱)	94 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	T22

CDM-TD 陶瓷放電管複金屬燈泡

認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	3.4 mg
汞 (Hg) 含量 (標稱)	3.4 mg
能源消耗 kWh/1000 h	71 kWh
EPREL 註冊碼	473326
產品資料	
下訂產品名稱	MASTERC CDM-TD 70W/830 RX7s 1CT/12
完整產品名稱	MASTERC CDM-TD 70W/830 RX7s 1CT/12


完整產品代碼	871150019782515
訂單代碼	928082205125
材質 Nr. (12NC)	928082205125
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500197825
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500197832

二维绘图




Product	D (max)	D O	C (max)
MASTERC CDM-TD 70W/830 RX7s 1CT/12	22 mm	8 mm	119.63 mm

光度数据



Light Distribution Diagram - MASTERC CDM-TD 70W/830 RX7s 1CT/12




Spectral Power Distribution Colour - MASTERC CDM-TD 70W/830 RX7s 1CT/12

CDM-TD 陶瓷放電管複金屬燈泡

壽命



Life Expectancy Diagram - MASTERC CDM-TD 70W/830 RX7s 1CT/12



Lumen Maintenance Diagram - MASTERC CDM-TD 70W/830 RX7s 1CT/12

