



# MASTER CityWhite CDO-TT



## MASTER CityWhite CDO-TT Plus 150W/828 E40

Ceramic metal halide Outdoor with clear tubular outer bulb

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electromagnetic control gear or electronic gear suitable to drive CDO lamps (e.g. HID-PV Xt CDO)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Warm restart time can be up to 15 minutes; T15 ignitors therefore advised
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Color rendering index (CRI)	
Cap-Base	E40		87
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	10 mm
Flux measurement reference	Sphere	Operating and Electrical	
Life to 50% Failures (Nom)	27,000 hour(s)	Power Consumption	148.5 W
Light Technical		Voltage (Nom)	99 V
Color Code	828 [CCT of 2800K]	Voltage (Nom)	99 V
Luminous Flux	16,400 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Chromaticity Coordinate X (Nom)	0.447	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	0.4	Bulb Finish	Clear
Correlated Color Temperature (Nom)	2800 K		
Luminous Efficacy (rated) (Nom)	110 lm/W		

MASTER CityWhite CDO-TT


Bulb Shape	T46
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	15.8 mg
Mercury (Hg) Content (Nom)	15.8 mg
Energy Consumption kWh/1000 h	149 kWh
EPREL Registration Number	473327

Product Data

Order product name	MASTER CityWh CDO-TT Plus 150W/828 E40
--------------------	--


Full product name	MASTER CityWhite CDO-TT Plus 150W/828 E40
Full product code	871829112034600
Order code	12034600
Material Nr. (12NC)	928082219231
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291120346
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291120353

Dimensional drawing




Product	D (max)	O	L	C (max)
MASTER CityWh CDO-TT Plus 150W/828 E40	47 mm	10 mm	132 mm	211 mm

Photometric data




Light Distribution Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40




Spectral Power Distribution Colour - MASTER CityWh CDO-TT Plus 150W/828 E40

MASTER CityWhite CDO-TT

Lifetime



Life Expectancy Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40



Lumen Maintenance Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40

