



MASTER CityWhite CDO-TT

MASTER CityWh CDO-TT Plus 150W/828 E40

Ceramic metal halide lamp with clear tubular outer bulb shape, used in outdoor offering pleasant white light

Warnings and Safety

- · Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- · Lamps may use electromagnetic control gear or electronic gear suitable to drive CDO lamps (e.g. HID-PV Xt CDO)
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)
- · Warm restart time can be up to 15 minutes; T15 ignitors therefore advised
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	E40 [E40]
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	27,000 hour(s)
Light Technical	
Color Code	828 [CCT of 2800K]
Luminous Flux	16,400 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.447
Chromaticity Coordinate Y (Nom)	0.4
Correlated Color Temperature (Nom)	2800 K

Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	87
Arc Length O (Nom)	10 mm
Operating and Electrical	
Power Consumption	148.5 W
Voltage (Nom)	99 V
Voltage (Nom)	99 V
Controls and Dimming	
Dimmable	Yes


Datasheet, 2023, April 14 data subject to change

MASTER CityWhite CDO-TT

Mechanical and Housing					
Bulb Finish	Clear				
Bulb Shape	T46 [T 46mm]				
Approval and Application					
Energy Efficiency Class	F				
Mercury (Hg) Content (Max)	15.8 mg				
Mercury (Hg) Content (Nom)	15.8 mg				
Energy Consumption kWh/1000 h	149 kWh				
EPREL Registration Number	473327				
Product Data					
Order product name	MASTER CityWh CDO-TT Plus 150W/828 E40				


Full product name	MASTER CityWh CDO-TT Plus 150W/828 E40
Full product code	871829112034600
Order code	928082219231
Material Nr. (12NC)	928082219231
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291120346
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291120353

Dimensional drawing




Product	D (max)	0	L	C (max)
MASTER CityWh CDO-TT Plus 150W/828 E40	47 mm	10 mm	132 mm	211 mm

Photometric data




Light Distribution Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40




Spectral Power Distribution Colour - MASTER CityWh CDO-TT Plus $150W/828\ E40$

MASTER CityWhite CDO-TT

Lifetime





Life Expectancy Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40

Lumen Maintenance Diagram - MASTER CityWh CDO-TT Plus 150W/828 E40

