



MasterColor CDM-T T6

MasterColor CDM-T 70W/830 G12 T6 CL

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T6 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G12	85 lm/W	
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	
Life to 50% Failures (Nom)	12,000 hour(s)	84	
Light Technical		Arc Length O (Nom)	
Color Code	830 [CCT of 3000K]	7 mm	
Color Designation	Warm White (WW)	Operating and Electrical	
Chromaticity Coordinate X (Nom)	0.432	Power Consumption	
Chromaticity Coordinate Y (Nom)	0.395	73.2 W	
Correlated Color Temperature (Nom)	3000 K	Voltage (Nom)	
		88 V	
		Voltage (Nom)	
		88 V	

MasterColor CDM-T T6

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T19
Approval and Application	
Mercury (Hg) Content (Nom)	4.6 mg
Energy Consumption kWh/1000 h	80 kWh



Product Data	
Order product name	CDM-T 70W/830 G12 T6 CL
Full product name	MasterColor CDM-T 70W/830 G12 T6 CL
Order code	223370
Material Nr. (12NC)	928082305115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677223373
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677223378

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM-T	13/16	0.75	5/16	2-3/16	2-1/4	2-1/4	4-1/16
70W/830 G12	inch	inch	inch	inch	inch	inch	inch
T6 CL							

Photometric data





Light Distribution Diagram - CDM-T 70W/830 G12 T6 CL

Spectral Power Distribution Colour - CDM-T 70W/830 G12 T6 CL

MasterColor CDM-T T6

Lifetime



Life Expectancy Diagram - CDM-T 70W/830 G12 T6 CL

Lumen Maintenance Diagram - CDM-T 70W/830 G12 T6 CL

