



MASTER CityWhite CDO-TT



MASTER CityWhite CDO-TT Plus 70W/942 E27

Ceramic metal halide Outdoor with clear tubular outer bulb

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electromagnetic control gear or electronic gear suitable to drive CDO lamps (e.g. HID-PV Xt CDO)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Warm restart time can be up to 15 minutes; T15 ignitors therefore advised
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	E27		90
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	7.75 mm
Flux measurement reference	Sphere	Operating and Electrical	
Life to 50% Failures (Nom)	20,000 hour(s)	Power Consumption	74.0 W
Light Technical		Voltage (Nom)	96 V
Color Code	942 [CCT of 4200K]	Voltage (Nom)	96 V
Luminous Flux	7,500 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	Yes
Chromaticity Coordinate X (Nom)	0.371	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	0.366	Bulb Finish	Clear
Correlated Color Temperature (Nom)	4200 K		
Luminous Efficacy (rated) (Nom)	101 lm/W		


MASTER CityWhite CDO-TT

Bulb Shape	T35
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	6.6 mg
Mercury (Hg) Content (Nom)	6.6 mg
Energy Consumption kWh/1000 h	74 kWh
EPREL Registration Number	473332

Product Data	
Order product name	MASTER CityWh CDO-TT Plus 70W/942 E27


Full product name	MASTER CityWhite CDO-TT Plus 70W/942 E27
Full product code	871869659679100
Order code	59679100
Material Nr. (12NC)	928082619230
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696596791
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696596807

Dimensional drawing




Product	D (max)	O	L	C (max)
MASTER CityWh CDO-TT Plus 70W/942 E27	36 mm	7.75 mm	102 mm	156 mm

Photometric data




Light Distribution Diagram - MASTER CityWh CDO-TT Plus 70W/942 E27




Spectral Power Distribution Colour - MASTER CityWh CDO-TT Plus 70W/942 E27

MASTER CityWhite CDO-TT

Lifetime



Lumen Maintenance Diagram - MASTER CityWh CDO-TT Plus 70W/942 E27



Life Expectancy Diagram - MASTER CityWh CDO-TT Plus 70W/942 E27

