



MASTERColour CDM-T

MASTERC CDM-T 35W/830 G12 1CT/12

系列单端紧凑型高光效放电灯在整个寿命期间具有稳定的光色和明亮通透的闪光

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G12
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	12,000 小时
灯技术	
颜色代码	830 [CCT of 3000K]
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.428
色度坐标 Y (标称)	0.397
相关色温 (标称)	3000 K
光效 (额定) (标称)	79 lm/W
显色指数 (CRI)	83


弧长 O (标称)	5 mm
操作和电气	
功耗	39.1 W
电压 (标称)	82 V
电压 (标称)	82 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明
灯泡外形	T19 [T 19 毫米]

MASTERColour CDM-T

审批和申请	
汞 (Hg) 含量 (标称)	3.1 mg
能耗 kWh/1000 h	43 kWh
产品数据	
订单产品名称	MASTERC CDM-T 35W/830 G12 1CT/12
完整的产品名称	MASTERC CDM-T 35W/830 G12 1CT/12
完整产品代码	871869648443200


订购代码	928083105129
材料编号 (12NC)	928083105129
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718696484432
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718696484449

二维绘图




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 35W/830 G12 1CT/12	20 mm	0.75 in	5 mm	55 mm	57 mm	56 mm	103 mm

光度数据





Light Distribution Diagram - MASTERC CDM-T 35W/830 G12 1CT/12



Spectral Power Distribution Colour - MASTERC CDM-T 35W/830 G12 1CT/12

MASTERC colour CDM-T

寿命



Lumen Maintenance Diagram - MASTER CDM-T 35W/830 G12 1CT/12

Life Expectancy Diagram - MASTER CDM-T 35W/830 G12 1CT/12

