



MASTER CosmoWhite CPO-TW & CPO-TW Xtra

MASTER CosmoWhite CPO-TW Xtra 45W/628 PGZ12

New-generation ceramic metal halide lamps used in Outdoor offering efficient and pleasant white light

Warnings and Safety

- · Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- · Use only with electronic control gear
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	PGZ12
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	32,000 hour(s)
Light Technical	
Color Code	628 [CCT of 2800K]
Luminous Flux	4,900 lm
Color Designation	White (WH)

Chromaticity Coordinate X (Nom)	0.447			
Chromaticity Coordinate Y (Nom)	0.4			
Correlated Color Temperature (Nom) 2800 K				
Luminous Efficacy (rated) (Nom)	110 lm/W			
Color rendering index (CRI)	66			
Arc Length O (Nom)	14 mm			
Operating and Electrical				
Power Consumption	44.5 W			
Voltage (Nom)	91 V			


Datasheet, 2023, April 16 data subject to change

MASTER CosmoWhite CPO-TW & CPO-TW Xtra

Voltage (Nom)	91 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T19
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	45 kWh
EPREL Registration Number	473336


Product Data					
Order product name	MST CosmoWh CPO-TW Xtra 45W/628 PGZ12				
Full product name	MASTER CosmoWhite CPO-TW Xtra 45W/628				
	PGZ12				
Full product code	871829115001500				
Order code	15001500				
Material Nr. (12NC)	928083805127				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8718291150015				
Numerator - Packs per outer box	12				
EAN/UPC - Case	8718291150022				

Dimensional drawing




Product	D (max)	D	0	L	C (max)
MST CosmoWh CPO-TW Xtra 45W/628	20 mm	19 mm	14 mm	59 mm	132 mm
PGZ12					

Photometric data









Light Distribution Diagram - MST CosmoWh CPO-TW Xtra 45W/628 PGZ12

MASTER CosmoWhite CPO-TW & CPO-TW Xtra

Lifetime





Lumen Maintenance Diagram - MST CosmoWh CPO-TW Xtra 45W/628 PGZ12

Life Expectancy Diagram - MST CosmoWh CPO-TW Xtra 45W/628 PGZ12



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.