



# Ecopassport

MASTERColour CDM-T

MASTERColour CDM-T 150W/942 G12 1CT



## Energy

- Power (Rated) (Nom) : 147 W
- Luminous Efficacy (rated) (Nom) : 84 lm/W
- Energy Efficiency Label (EEL) : A
- Dimmable : No



## Substances

- Mercury (Hg) Content (Nom) : 10.4 mg



## lifetime

- Life To 10% Failures (Nom) : 10000 h
- Life to 20% Failures (Nom) : 11000 h
- Life to 5% Failures (Nom) : 9000 h
- Life to 50% Failures (Nom) : 12000 h

[field not found 'specificationOverviewText\_title']

### Our environmental product specifications overview

At Philips, we strive to make the world healthier and more sustainable through innovation. Our sustainability efforts are globally recognized and reflected e.g., by our continuous leading positions global rankings like the Dow Jones Sustainability Index and the Carbon Disclosure Project. In our eco-design process we focus on Energy, Weight, Recycling, Packaging, Substances, and Reliability to view and further

# PHILIPS

2018, December 11  
data subject to change  
Order code : 928084605131