



MASTERColour CDM-TD

MASTERC CDM-TD 150W/942 RX7s 1CT

系列双端紧凑型高光效放电灯在整个寿命期间具有稳定的光色和明亮通透的闪光

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息		弧长 ϕ (标称)	
底盖	RX7s	10 mm	
操作位置	P45 [并行 +/-45D 或水平 (HOR)]	操作和电气	
光通量测量参考	Sphere	功耗	152.0 W
50% 故障条件下的使用寿命 (标称)	16,000 小时	电压 (标称)	103 V
		电压 (标称)	103 V
灯技术		控制和调光	
颜色代码	942 [CCT of 4200K]	可调光	否
光通量	13,650 lm	机械和外壳	
颜色名称	冷白色 (CW)	灯泡外观	透明
色度坐标 X (标称)	0.371	灯泡外形	T22
色度坐标 Y (标称)	0.366		
相关色温 (标称)	4200 K		
光效 (额定) (标称)	90 lm/W		
显色指数 (CRI)	96		


MASTERC colour CDM-TD

审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	8.3 mg
汞 (Hg) 含量 (标称)	8.29 mg
能耗 kWh/1000 h	152 kWh
EPREL 注册号	473340

产品数据	
订单产品名称	MASTERC CDM-TD 150W/942 RX7s 1CT
完整的产品名称	MASTERC CDM-TD 150W/942 RX7s 1CT


完整产品代码	871150020025915
订购代码	928084805133
材料编号 (12NC)	928084805133
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500200259
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8711500200266

二维绘图




Product	D (max)	D O	C (max)
MASTERC CDM-TD 150W/942 RX7s 1CT	22 mm	10 mm	137.43 mm

光度数据





Light Distribution Diagram - MASTERC CDM-TD 150W/942 RX7s 1CT



Spectral Power Distribution Colour - MASTERC CDM-TD 150W/942 RX7s 1CT

MASTERColour CDM-TD

寿命



Life Expectancy Diagram - MASTERC CDM-TD 150W/942 RX7s 1CT

Lumen Maintenance Diagram - MASTERC CDM-TD 150W/942 RX7s 1CT

