# **PHILIPS** Lighting



# MasterColor CDM-TC T4

# MasterColor CDM-TC 35W/830 G8.5 T4 CL

MasteColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T4 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

#### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

#### **Product data**


General Information		Luminous Efficacy (rated) (Nom)	79 lm/W	
Cap-Base	G8.5	Color rendering index (CRI)	81	
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	5 mm	
Life to 50% Failures (Nom)	12,000 hour(s)			
		Operating and Electrical		
Light Technical		Power Consumption	39.1 W	
Color Code	830 [CCT of 3000K]	Voltage (Nom)	88 V	
Color Designation	Warm White (WW)	Voltage (Nom)	88 V	
Chromaticity Coordinate X (Nom)	0.432			
Chromaticity Coordinate Y (Nom)	0.394			
Correlated Color Temperature (Nom)	3000 K			

### MasterColor CDM-TC T4


Controls and Dimming				
Dimmable	No			
Mechanical and Housing				
Bulb Finish	Clear			
Bulb Material	UV-Block Quartz			
Bulb Shape	T14			
Approval and Application				
Mercury (Hg) Content (Nom)	3.1 mg			
Energy Consumption kWh/1000 h	43 kWh			


Product Data	
Order product name	CDM-TC 35W/830 G8.5 T4 CL
Full product name	MasterColor CDM-TC 35W/830 G8.5 T4 CL
Order code	373720
Material Nr. (12NC)	928085205115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677373726
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677373721

#### Dimensional drawing




#### Photometric data





Light Distribution Diagram - CDM-TC 35W/830 G8.5 T4 CL


Product	D (max)	D	0	L (min)	L (max)	L	C (max)
CDM-TC	5/8 inch	0.5	1/4	2-1/16	2-1/8	2-1/16	3-3/8
35W/830 G8.5		inch	inch	inch	inch	inch	inch
T4 CL							



Spectral Power Distribution Colour - CDM-TC 35W/830 G8.5 T4 CL

## MasterColor CDM-TC T4

Lifetime



Lumen Maintenance Diagram - CDM-TC 35W/830 G8.5 T4 CL

Life Expectancy Diagram - CDM-TC 35W/830 G8.5 T4 CL



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, November 3 - data subject to change