



# CDM-SA/T

## CDM-SA/T 150W/942 1CT/12

CDM-SA/T – the greener way to light up the night With a high luminous efficacy producing more lumens per watt than standard Architainment lamps, the CDM-SA/T is the greener alternative to light up the night. In addition, the optimal lamp filling and short arc of the lamp create a high beam intensity and excellent colour rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Color rendering index (CRI)	
Cap-Base	G12 [G12]		95
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	6 mm
Flux measurement reference	Sphere	Operating and Electrical	
Life to 50% Failures (Nom)	9,000 hour(s)	Power Consumption	155.0 W
		Lamp Current (Nom)	1.8 A
Light Technical		Controls and Dimming	
Color Code	942 [CCT of 4200K]	Dimmable	No
Luminous Flux	13,000 lm	Approval and Application	
Color Designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.371	Mercury (Hg) Content (Max)	11.9 mg
Chromaticity Coordinate Y (Nom)	0.366	Energy Consumption kWh/1000 h	155 kWh
Correlated Color Temperature (Nom)	4200 K		
Luminous Efficacy (rated) (Nom)	84 lm/W		

## CDM-SA/T

EPREL Registration Number	897559
<b>Product Data</b>	
Order product name	CDM-SA/T 150W/942 1CT/12
Full product name	CDM-SA/T 150W/942 1CT/12
Full product code	871150020094515
Order code	928086605103


Material Nr. (12NC)	928086605103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500200945
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500200952

### Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
CDM-SA/T	20 mm	6	55 mm	57 mm	56	110 mm	31 mm	30	29 mm
150W/942		mm			mm			mm	
1CT/12									

### Photometric data



Spectral Power Distribution Colour - CDM-SA/T 150W/942 1CT/12

