



# CDM

## CDM-SA/R 150W/942 UNP/1

Compact reflector discharge lamps with quartz outer bulb

### Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	CERAMICCAP-CABLE [Ceramic Cap-Cable (C)]
Operating position	UNIVERSAL [Any or Universal (U)]
Life to 50% failures (nom.)	6,000 h
Light Technical	
Colour Code	942 [CCT of 4200K]
Luminous flux (min.)	2,295 lm
Luminous Flux	2,550 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.366
Chromaticity Coordinate Y (Nom)	0.353
Correlated Colour Temperature	4200 K
Luminous efficacy (rated) (nom.)	16.1 lm/W
Colour rendering index (CRI)	96
Operating and Electrical	
Power Consumption	158.0 W
Lamp current (nom.)	1.76 A


Voltage (nom.)	106 V
Voltage (nom.)	106 V
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	CDM-SA/R 150W/942 UNP/1
Full product name	CDM-SA/R 150W/942 UNP/1
Full EOC	871150020150800
Order code	20150800
Material no. (12 NC)	928086805303
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900783490
Numerator – packs per outer box	1
EAN/UPC – Case	8711500201508

Dimensional drawing



Product	D (max)	X	C (max)
CDM-SA/R 150W/942 UNP/1	95.3 mm	280 mm	106 mm

Photometric data



Spectral Power Distribution Colour - CDM-SA/R 150W/942 UNP/1

