



MASTERColour CDM-R

MASTERColour CDM-R 70W/942 E27 PAR30L 10D 1CT

Range of compact, high-efficiency, discharge reflector lamps with a stable color over lifetime and a crisp, sparkling light

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	E27 [E27]	93	
Operating Position	UNIVERSAL [Any or Universal (U)]	LLMF At End Of Nominal Lifetime (Nom) 61 %	
Switching Cycle	1,050	Luminous Flux in 90° Cone (Rated) 4,000 lm	
Life to 50% Failures (Nom)	12,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	942 [CCT of 4200K]	Power Consumption	73 W
Beam Angle (Nom)	10 degree(s)	Warm-up time to 60% light	120 s
Luminous Intensity (Nom)	60,000 cd	Voltage (Nom)	88 V
Color Designation	Cool White (CW)	Voltage (Nom)	88 V
Chromaticity Coordinate X (Nom)	0.371	Controls and Dimming	
Chromaticity Coordinate Y (Nom)	0.366	Dimmable	No
Correlated Color Temperature (Nom)	4200 K		

MASTERC colour CDM-R

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and Application	
Mercury (Hg) Content (Nom)	6.6 mg
Energy Consumption kWh/1000 h	80 kWh
Product Data	
Order product name	MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT

Full product name	MASTERC colour CDM-R 70W/942 E27 PAR30L 10D 1CT
Full product code	692059027236300
Order code	27236300
Material Nr. (12NC)	928089300693
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6920590272363
Numerator - Packs per outer box	6
EAN/UPC - Case	6920590273292


Dimensional drawing



Product	D (max)	D	C (max)	C
MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT	97 mm	95 mm	123 mm	120 mm

Photometric data

112° / 180° / 120°




Light Distribution Diagram - MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT


Spectral Power Distribution Colour - MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT

MASTERC colour CDM-R

Lifetime



Life Expectancy Diagram - MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT



Lumen Maintenance Diagram - MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT

