



# MASTERColour CDM-T



## MASTERColour CDM-T 35W/842 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Luminous efficacy (rated) (nom.)	
Cap base	G12	77 lm/W	
Operating position	UNIVERSAL [Any or Universal (U)]	Colour rendering index (CRI)	
Flux measurement reference	Sphere	84	
Life to 50% failures (nom.)	12,000 h	Arc Length O (Nom)	
Light Technical		5 mm	
Colour Code	842 [CCT of 4200K]	Operating and Electrical	
Luminous Flux	3,000 lm	Power Consumption	39.1 W
Colour designation	Cool White (CW)	Voltage (nom.)	85 V
Chromaticity Coordinate X (Nom)	0.371	Voltage (nom.)	85 V
Chromaticity Coordinate Y (Nom)	0.366	Controls and Dimming	
Correlated Colour Temperature	4200 K	Dimmable	No

## MASTERCcolour CDM-T

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T19

## Approval and Application


Energy Efficiency Class	G
Mercury (Hg) content (max.)	2.7 mg
Mercury (Hg) content (nom.)	2.7 mg
Energy consumption kWh/1,000 hours	40 kWh
EPREL registration number	473355

## Product Data

Order product name	MASTERC CDM-T 35W/842 G12 1CT/12
--------------------	----------------------------------


<b>Full product name</b>	MASTERColour CDM-T 35W/842 G12 1CT/12
<b>Full EOC</b>	871150021126215
<b>Order code</b>	21126215
<b>Material no. (12 NC)</b>	928094305125
<b>Local order code</b>	35CDMT842
<b>SAP numerator – quantity per pack</b>	1
<b>EAN/UPC – Product/Case</b>	8711500211262
<b>Numerator – packs per outer box</b>	12
<b>EAN/UPC - Case</b>	8711500211279

## Dimensional drawing





Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 35W/842	20 mm	0.75 in	5 mm	55 mm	57 mm	56 mm	103 mm
G12 1CT/12							


## Photometric data




**Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12**



**Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12**




Photometric data



Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12


Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12



Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12

Spectral Power Distribution Colour - MASTERC CDM-T 35W/842 G12 1CT/12

Lifetime



Life Expectancy Diagram - MASTERC CDM-T 35W/842 G12 1CT/12

## MASTERColour CDM-T

