

PHILIPS

Lighting



# MASTERCcolour CDM-R 陶瓷複金屬燈

## MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT

精巧、高效率放電式反射燈具，光色歷久如新，光線清晰明亮

### 安全提示

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

一般資訊	
燈座基底	E26 [Single Contact Medium Screw]
操作位置	UNIVERSAL [任何或通用 (U)]
壽命 (故障率 50%) (標稱)	12,000 h
照明技術	
色碼	942 [CCT of 4200K]
光束角 (Nom)	30 °
光強 (標稱)	13,000 cd
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	0.371
色度坐標 Y (Nom)	0.366
相關色彩溫度 (規範)	4200 K
演色性指數 (CRI)	93
運轉與電力	
耗電量	73 W


電壓 (標稱)	88 V
電壓 (標稱)	88 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	PAR30L [PAR 3.75 inch/95mm (長型)]
認證與應用	
汞 (Hg) 含量 (標稱)	6.6 mg
能源消耗 kWh/1000 h	80 kWh
產品資料	
下訂產品名稱	MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT
完整產品名稱	MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT

# MASTERC colour CDM-R 陶瓷複金屬燈

完整產品代碼	872790088730300
訂單代碼	928094500610
材質 Nr. (12NC)	928094500610
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8727900887303


分子 - 每一外盒包裝	6
EAN/UPC - 箱	8727900887310

## 二维绘图




Product	D (max)	D	C (max)	C
MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT	97 mm	95 mm	123 mm	118 mm

## 光度数据




Light Distribution Diagram - MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT




Spectral Power Distribution Colour - MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT

## 壽命



Life Expectancy Diagram - MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT



Lumen Maintenance Diagram - MASTERC CDM-R 70W/942 E26 PAR30L 30D 1CT

## MASTERCcolour CDM-R 陶瓷複金屬燈

