



MASTERColour CDM-T Elite

MASTERC CDM-T Elite 150W/930 G12 1CT/12

Single-ended, high-efficiency Ceramic Metal Halide discharge lamp

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Arc Length O (Nom)	
Cap-Base	G12	9 mm	
Operating Position	P10 [Parallel +/-10D or Horizontal(HOR)]		
Flux measurement reference	Sphere		
Life to 50% Failures (Nom)	12,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	930 [CCT of 3000K]	Power Consumption	150.1 W
Luminous Flux	14,600 lm	Voltage (Nom)	92 V
Color Designation	Warm White (WW)	Voltage (Nom)	92 V
Chromaticity Coordinate X (Nom)	0.434		
Chromaticity Coordinate Y (Nom)	0.398		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	98 lm/W		
Color rendering index (CRI)	92		
		Controls and Dimming	
		Dimmable	No
		Mechanical and Housing	
		Bulb Finish	Clear
		Bulb Shape	T19

MASTERC colour CDM-T Elite

Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	9.5 mg
Mercury (Hg) Content (Nom)	9.5 mg
Energy Consumption kWh/1000 h	151 kWh
EPREL Registration Number	473357
Product Data	
Order product name	MASTERC CDM-T Elite 150W/930 G12 1CT/12
Full product name	MASTERC CDM-T Elite 150W/930 G12 1CT/12


Full product code	871150021312915
Order code	928094705125
Material Nr. (12NC)	928094705125
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500213129
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500213136

Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 150W/930 G12 1CT/12	20 mm	9 mm	55 mm	57 mm	56 mm	110 mm

Photometric data




Light Distribution Diagram - MASTERC CDM-T Elite 150W/930 G12 1CT/12




Spectral Power Distribution Colour - MASTERC CDM-T Elite 150W/930 G12 1CT/12

MASTERC colour CDM-T Elite

Lifetime



Life Expectancy Diagram - MASTERC CDM-T Elite 150W/930 G12 1CT/12



Lumen Maintenance Diagram - MASTERC CDM-T Elite 150W/930 G12 1CT/12

