



MSD

MSD 200/2 1CT/4

These single ended, compact lamps enable optimal light collection and accurate beam control, while they also provide true daylight color temperatures – all to create great stage brightness and vivid entertainment. And since they offer long lifetime usage they help minimize the cost of ownership via fewer lamp replacements and fewer maintenance man hour costs.

安全提示


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	GY9.5 [GY9.5]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	3,000 小时
灯技术	
颜色代码	670 (2)
光通量 (最低)	11,340 lm
光通量	12,600 lm
色度坐标 X (标称)	313
色度坐标 Y (标称)	315
相关色温 (标称)	6600 K
光效 (额定) (标称)	63 lm/W
显色指数 (CRI)	70
弧长 O (标称)	5.0 mm


操作和电气	
功耗	200 W
灯具电流 (标称)	3.4 A
控制和调光	
可调光	否
产品数据	
订单产品名称	MSD 200/2 1CT/4
完整的产品名称	MSD 200/2 1CT/4
完整产品代码	871869641590000
订购代码	928097605115
材料编号 (12NC)	928097605115
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718696415900
计算器 - 每个外包装箱中的包数	4
EAN/UPC - 案例	8718696415917

二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 200/2	23 mm	5.0	54 mm	56 mm	55	108 mm	29 mm	28	27 mm
1CT/4		mm			mm			mm	

光度数据



Spectral Power Distribution Colour - MSD 200/2 1CT/4

