



MSR Hot Restrike

MSR 575 HR 1CT/4

High-efficiency hot restrike metal halide lamps designed for optimum light collection

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information					
Cap-Base	G22 [G22]				
Operating Position	UNIVERSAL [Any or Universal (U)]				
Life to 50% Failures (Nom)	1,000 h				
Light Technical					
Color Code	- [Not Specified]				
Luminous Flux (Min)	43,200 lm				
Luminous Flux	48,000 lm				
Chromaticity Coordinate X (Nom)	323				
Chromaticity Coordinate Y (Nom)	328				
Correlated Color Temperature (Nom)	6000 K				
Luminous Efficacy (Rated) (Min)	75 lm/W				
Luminous Efficacy (rated) (Nom)	83 lm/W				
Color rendering index (CRI)	90				
Arc Length O (Nom)	7.0 mm				
Operating and Electrical					
Power Consumption	575 W				

Lamp Current (Nom)	6.75 A				
Controls and Dimming					
Dimmable	Yes				
Product Data					
Order product name	MSR 575 HR 1CT/4				
Full product name	MSR 575 HR 1CT/4				
Full product code	871829122105000				
Local code description	MSR575HR				
Order code	928097705115				
Material Nr. (12NC)	928097705115				
Local order code	MSR575HR				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8718291221050				
Numerator - Packs per outer box	4				
EAN/UPC - Case	8718291221067				

Datasheet, 2023, April 16 data subject to change


MSR Hot Restrike

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575	30 mm	7.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/4		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSR 575 HR 1CT/4



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.