



# Eco passport

MASTER MHN-SA

MASTER MHN-SA 1800W/956 230V XW UNP/1



## Energy

- Power (Rated) (Nom) : 1800.0 W
- Luminous efficacy (rated) (nom.) : 86 lm/W
- Energy efficiency label (EEL) : A+
- Dimmable : No



## Substances

- Mercury (Hg) content (nom.) : 92 mg



## Lifetime

- Life to 10% failures (nom.) : 2300 h
- Life to 20% failures (nom.) : 3000 h
- Life to 5% failures (nom.) : 1800 h
- Life to 50% failures (nom.) : 5000 h