



MSR Gold™ SA Double Ended

MSR Gold 1200 SA/DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	SFC10-4 [SFC10-4]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	103,000 lm
Chromaticity Coordinate X (Nom)	326
Chromaticity Coordinate Y (Nom)	332
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (Rated) (Min)	77 lm/W
Luminous Efficacy (rated) (Nom)	86 lm/W


Color rendering index (CRI)	83
Arc Length O (Nom)	7.0 mm
Operating and Electrical	
Power Consumption	1,200 W
Lamp Current (Nom)	13.6 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSR Gold 1200 SA/DE 1CT/4
Full product name	MSR Gold 1200 SA/DE 1CT/4

MSR Gold™ SA Double Ended

Full product code	871829122121000
Order code	928099605115
Material Nr. (12NC)	928099605115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221210


Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221227

Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold 1200 SA/DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 1200 SA/DE 1CT/4

