



MasterColor CDM-TC T4

MasterColor CDM-TC 35W/842 G8.5.1CT/12

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T4 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Product data

General Information	
Base	G8.5 [G8.5]
Operating Position	Universal [Universal]
Life to 5% Failures (Nom)	6000 h
Life To 10% Failures (Nom)	10000 h
Life to 20% Failures (Nom)	9000 h
Life to 50% Failures (Nom)	12000 h
ANSI Code HID	C130/E
Light Technical	
Color Code	842 [CCT of 4200K]
Luminous Flux (Rated) (Nom)	3100 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	70 %
Lumen Maintenance 2000 h (Min)	75 %
Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Min)	70 %
Lumen Maintenance 5000 h (Nom)	80 %
Chromaticity Coordinate X (Nom)	0.370
Chromaticity Coordinate Y (Nom)	0.365

Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	79 lm/W
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Min)	39.0 W
Power (Rated) (Nom)	35 W
Ignition Supply Voltage (Max)	198 V
Ignition Supply Voltage (Min)	198 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	30 s
Voltage (Max)	93 V
Voltage (Min)	77 V
Voltage (Nom)	85 V
Controls and Dimming	
Dimmable	No
Run-Up Time 90% (Max)	3 min

MasterColor CDM-TC T4


Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	UV-Block Quartz
Approval and Application	
Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	2.7 mg
Energy Consumption kWh/1000 h	43 kWh
UV	
Pet (Niosh) (Min)	8 h/500lx
Damage Factor D/fc (Max)	0.5
Luminaire Design Requirements	
Bulb Temperature (Max)	500 °C

Pinch Temperature (Max)	300 °C
Product Data	
Order product name	MasterColor CDM-TC 35W/842 G8.5.1CT/12
EAN/UPC - Product	046677208837
Order code	208835
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928099905115
Net Weight (Piece)	0.010 kg
ILCOS Code	MT/UB-35/842-H-G8.5-17/85

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing




CDM-TC 35W/842 G8.5


Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MasterColor CDM-TC 35W/842 G8.5.1CT/12	15 mm	0.5 in	5 mm	51 mm	53 mm	52 mm	85 mm

MasterColor CDM-TC T4

Photometric data



Lifetime



LDLE_CDM-TC_0001-Life expectancy diagram

