



MSR Gold™ FastFit

MSR Gold™ 700 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | Arc Length O (Nom) | |
|------------------------------------|----------------------------------|--------------------------|-----------------------------|
| Cap-Base | PGJX50 [PGJX50] | 3.8 mm | |
| Operating Position | UNIVERSAL [Any or Universal (U)] | | |
| Life to 50% Failures (Nom) | 750 hour(s) | | |
| Light Technical | | Operating and Electrical | |
| Luminous Flux | 54,000 lm | Power Consumption | 700 W |
| Chromaticity Coordinate X (Nom) | 327 | Lamp Current (Nom) | 10.2 A |
| Chromaticity Coordinate Y (Nom) | 336 | | |
| Correlated Color Temperature (Nom) | 6000 K | Controls and Dimming | |
| Luminous Efficacy (rated) (Nom) | 76 lm/W | Dimmable | Yes |
| Color rendering index (CRI) | 79 | | |
| | | Product Data | |
| | | Order product name | MSR Gold 700 FastFit 1CT/4 |
| | | Full product name | MSR Gold™ 700 FastFit 1CT/4 |

MSR Gold™ FastFit

| | |
|-------------------------------|-----------------|
| Full product code | 871829122119700 |
| Order code | 22119700 |
| Material Nr. (12NC) | 928106005115 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291221197 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718291221203 |

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F |
|----------------------------|---------|--------|---------|---------|-------|---------|-------|
| MSR Gold 700 FastFit 1CT/4 | 23.2 mm | 3.8 mm | 64 mm | 66 mm | 65 mm | 112 mm | 50 mm |

Photometric data



Spectral Power Distribution Colour - MSR Gold 700 FastFit 1CT/4

