



MSR Gold™ FastFit

MSR Gold™ 700 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Product data

General Information		Operating and Electrical	
Base	PGJX50 [PGJX50]	Power (Rated) (Nom)	700 W
Operating Position	Universal [Universal]	Lamp Current (Nom)	10.2 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	198 V
Life to 50% Failures (Nom)	750 h		
System Description	FastFit	Controls and Dimming	
		Dimmable	Yes
Light Technical		Mechanical and Housing	
Initial lumen (Min)	45500 lm	Cap-Base Information	PGJX50
Initial lumen (Nom)	50000 lm		
Chromaticity Coordinate X (Nom)	327	Luminaire Design Requirements	
Chromaticity Coordinate Y (Nom)	336	Bulb Temperature (Max)	950 °C
Correlated Color Temperature (Nom)	6000 K	Pinch Temperature (Max)	500 °C
Luminous Efficacy (rated) (Nom)	71 lm/W		
Color Rendering Index (Nom)	80	Product Data	
		Order product name	MSR Gold™ 700 FastFit 1CT/4


MSR Gold™ FastFit

EAN/UPC - Product	8718291221197
Order code	286914
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Material Nr. (12NC)	928106005115
Net Weight (Piece)	0.100 kg

Warnings and Safety

Dimensional drawing





MSR GOLD 700 FastFit

Product

MSR Gold™ 700 FastFit 1CT/4

Photometric data



XDPB_XDMSR_0001-Spectral power distribution B/W

