



MSR Gold™ FastFit

MSR Gold™ 2000/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information					
- Ceneral Information					
Cap-Base	PGJX50 [PGJX50]				
Operating Position	UNIVERSAL [Any or Universal (U)]				
Life to 50% Failures (Nom)	750 hour(s)				
Light Technical					
Color Code	2				
Luminous Flux	157,000 lm				
Chromaticity Coordinate X (Nom)	297				
Chromaticity Coordinate Y (Nom)	322				
Correlated Color Temperature (Nom)	7500 K				
Luminous Efficacy (rated) (Nom)	78 lm/W				

Color rendering index (CRI)	88				
Arc Length O (Nom)	8.0 mm				
Operating and Electrical					
Power Consumption	2,000 W				
Lamp Current (Nom)	15.4 A				
Controls and Dimming					
Dimmable	Yes				
Product Data					
Order product name	MSR Gold 2000/2 FastFit 1CT/8				


Datasheet, 2023, April 16 data subject to change

MSR Gold™ FastFit

Full product name	MSR Gold™ 2000/2 FastFit 1CT/8
Full product code	872790090830500
Order code	90830500
Material Nr. (12NC)	928106105114
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8727900908305
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900908312

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F
MSR Gold 2000/2 FastFit	34 mm	8.0 mm	66 mm	68 mm	67 mm	134 mm	50 mm
1CT/8							

