



# MSR Gold™ FastFit

## MSR Gold™ 2000/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

### Product data

General Information	
Cap base	PGJX50 [ PGJX50]
Operating position	UNIVERSAL [ Any or Universal (U)]
Main application	Entertainment
Life to 50% failures (nom.)	750 h
System description	FastFit
Light Technical	
Colour code	2
Luminous flux (min.)	138000 lm
Luminous flux (nom.)	160000 lm
Chromaticity coordinate X (nom.)	297
Chromaticity coordinate Y (nom.)	322
Correlated Colour Temperature (Nom)	7500 K
Luminous efficacy (rated) (nom.)	80 lm/W
Color rendering index (nom.)	88

Operating and Electrical	
Power (Rated) (Nom)	2000 W
Lamp current (nom.)	15.4 A
Ignition supply voltage (min.)	198 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap base information	PGJX50
Luminaire Design Requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	500 °C
Product Data	
Full product code	872790090830500

## MSR Gold™ FastFit

Order product name	MSR Gold™ 2000/2 FastFit 1CT/8
EAN/UPC – product	8727900908305
Order code	90830500
Numerator – quantity per pack	1
Numerator – packs per outer box	8

Material no. (12NC)	928106105114
Net weight (piece)	0.147 kg

### Warnings and Safety

### Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 2000/2 FastFit 1CT/8	34 mm	8.0 mm	66 mm	68 mm	67 mm	134 mm	50 mm

MSR GOLD 2000/2 FastFit

