



MSR Gold™ FastFit

MSR Gold 2000/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	PGJX50
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Color Code	2
Luminous Flux	157,000 lm
Chromaticity Coordinate X (Nom)	297
Chromaticity Coordinate Y (Nom)	322
Correlated Color Temperature (Nom)	7500 K
Luminous Efficacy (rated) (Nom)	78 lm/W


Color rendering index (CRI)	88
Arc Length O (Nom)	8.0 mm
Operating and Electrical	
Power Consumption	2,000 W
Lamp Current (Nom)	15.4 A
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 2000/2 FastFit 1CT/8

MSR Gold™ FastFit

Full product name	MSR Gold 2000/2 FastFit 1CT/8
Full product code	872790090830500
Order code	928106105114
Material Nr. (12NC)	928106105114
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8727900908305
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900908312

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 2000/2 FastFit 1CT/8	34 mm	8.0 mm	66 mm	68 mm	67 mm	134 mm	50 mm

