



MSR Gold™ FastFit

MSR Gold 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	PGJX50	Arc Length O (Nom)	73
Operating Position	UNIVERSAL [Any or Universal (U)]		3.8 mm
Life to 50% Failures (Nom)	750 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	700 W
Color Code	2	Lamp Current (Nom)	10.2 A
Luminous Flux	48,000 lm	Controls and Dimming	
Chromaticity Coordinate X (Nom)	298	Dimmable	Yes
Chromaticity Coordinate Y (Nom)	322	Product Data	
Correlated Color Temperature (Nom)	7500 K	Order product name	MSR Gold 700/2 FastFit 1CT/8
Luminous Efficacy (rated) (Nom)	68 lm/W		

MSR Gold™ FastFit

Full product name	MSR Gold 700/2 FastFit 1CT/8
Full product code	872790090850300
Order code	928106205114
Material Nr. (12NC)	928106205114
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8727900908503
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900908510

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 700/2 FastFit 1CT/8	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 700/2 FastFit 1CT/8

