



MSR Gold™ FastFit

MSR Gold™ 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Correlated Color Temperature (Nom)	
Cap-Base	PGJX50	Luminous Efficacy (rated) (Nom)	7500 K
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	68 lm/W
Life to 50% Failures (Nom)	750 hour(s)	Arc Length O (Nom)	73
Light Technical		Operating and Electrical	
Color Code	2	Power Consumption	3.8 mm
Luminous Flux	48,000 lm	Lamp Current (Nom)	700 W
Chromaticity Coordinate X (Nom)	298		10.2 A
Chromaticity Coordinate Y (Nom)	322		

MSR Gold™ FastFit

Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 700/2 FastFit 1CT/8
Full product name	MSR Gold™ 700/2 FastFit 1CT/8
Full product code	872790090850300
Order code	245621


Material Nr. (12NC)	928106205114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900908503
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900908510

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold	15/16	3/16	2-9/16	2-5/8	2-9/16	4-7/16	2 inch
700/2 FastFit	inch	inch	inch	inch	inch	inch	
1CT/8							

Photometric data



Spectral Power Distribution Colour - MSR Gold 700/2 FastFit 1CT/8

