



MSR Gold™ FastFit

MSR Gold™ 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Product data

| General Information | | Operating and Electrical | |
|------------------------------------|------------------------|-------------------------------|-------------------------------|
| Base | PGJX50 [PGJX50] | Power (Rated) (Nom) | 700 W |
| Operating Position | Universal [Universal] | Lamp Current (Nom) | 10.2 A |
| Main Application | Entertainment | Ignition Supply Voltage (Min) | 198 V |
| Life to 50% Failures (Nom) | 750 h | | |
| System Description | FastFit | | |
| Light Technical | | Controls and Dimming | |
| Color Code | 2 | Dimmable | Yes |
| Initial lumen (Min) | 41800 lm | | |
| Initial lumen (Nom) | 50000 lm | Mechanical and Housing | |
| Chromaticity Coordinate X (Nom) | 298 | Cap-Base Information | PGJX50 |
| Chromaticity Coordinate Y (Nom) | 322 | | |
| Correlated Color Temperature (Nom) | 7500 K | Luminaire Design Requirements | |
| Luminous Efficacy (rated) (Nom) | 71 lm/W | Bulb Temperature (Max) | 950 °C |
| Color Rendering Index (Nom) | 75 | Pinch Temperature (Max) | 500 °C |
| | | Product Data | |
| | | Order product name | MSR Gold™ 700/2 FastFit 1CT/8 |


MSR Gold™ FastFit

| | |
|---------------------------------|---------------|
| EAN/UPC - Product | 8727900908503 |
| Order code | 245621 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 8 |

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 928106205114 |
| Net Weight (Piece) | 0.100 kg |

Warnings and Safety

Dimensional drawing





MSR GOLD 700/2 FastFit

Product

MSR Gold™ 700/2 FastFit 1CT/8

Photometric data



XDPB_XDMSR_0001-Spectral power distribution B/W

