



MSR Gold™ FastFit

MSR Gold™ 1500 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Product data

| General Information | |
|------------------------------------|------------------------|
| Base | PGJX50 [PGJX50] |
| Operating Position | Universal [Universal] |
| Main Application | Entertainment |
| Life to 50% Failures (Nom) | 750 h |
| System Description | FastFit |
| Light Technical | |
| Initial lumen (Min) | 100600 lm |
| Initial lumen (Nom) | 120000 lm |
| Chromaticity Coordinate X (Nom) | 323 |
| Chromaticity Coordinate Y (Nom) | 333 |
| Correlated Color Temperature (Nom) | 6000 K |
| Luminous Efficacy (rated) (Nom) | 80 lm/W |
| Color Rendering Index (Nom) | 80 |

| Operating and Electrical | |
|-------------------------------|--------|
| Power (Rated) (Nom) | 1500 W |
| Lamp Current (Nom) | 15.3 A |
| Ignition Supply Voltage (Min) | 198 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|--------|
| Cap-Base Information | PGJX50 |

| Luminaire Design Requirements | |
|-------------------------------|--------|
| Bulb Temperature (Max) | 950 °C |
| Pinch Temperature (Max) | 500 °C |

| Product Data | |
|--------------------|------------------------------|
| Order product name | MSR Gold™ 1500 FastFit 1CT/4 |

MSR Gold™ FastFit

| | |
|---------------------------------|---------------|
| EAN/UPC - Product | 8718291221340 |
| Order code | 286971 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 4 |

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 928107305115 |
| Net Weight (Piece) | 0.131 kg |

Warnings and Safety



Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F |
|---------------------------------|---------|--------|---------|---------|-------|---------|-------|
| MSR Gold™ 1500 FastFit 1CT/4 | 28 mm | 6.3 mm | 64 mm | 66 mm | 65 mm | 128 mm | 50 mm |

MSR GOLD 1500 FastFit

Photometric data



XDPB_XDMSR_0002-Spectral power distribution B/W

XDPO_XDMSR_0002-Spectral power distribution Colour

