



MSR Gold™ FastFit

MSR Gold 1500 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Arc Length O (Nom)	
Cap-Base	PGJX50	6.3 mm	
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	750 hour(s)	Power Consumption	1,500 W
		Lamp Current (Nom)	15.3 A
Light Technical		Controls and Dimming	
Luminous Flux	119,550 lm	Dimmable	Yes
Chromaticity Coordinate X (Nom)	323	Product Data	
Chromaticity Coordinate Y (Nom)	333	Order product name	MSR Gold 1500 FastFit 1CT/4
Correlated Color Temperature (Nom)	6000 K	Full product name	MSR Gold 1500 FastFit 1CT/4
Luminous Efficacy (rated) (Nom)	80 lm/W		
Color rendering index (CRI)	80		

MSR Gold™ FastFit

Full product code	871829122134000
Order code	928107305115
Material Nr. (12NC)	928107305115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221340


Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221357

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 1500 FastFit 1CT/4	28 mm	6.3 mm	64 mm	66 mm	65 mm	128 mm	50 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 1500 FastFit 1CT/4

