



# MSR Gold™ FastFit

## MSR Gold™ 1500/1 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

### Product data

General Information		Colour Rendering Index,horiz (Nom)	
Cap base	PGJX50 [ PGJX50]		85
Burning Position	UNIVERSAL [ Any/Universal]	Operating and Electrical	
Main application	Entertainment	Power (Rated) (Nom)	1500.0 W
Life to 50% failures (nom.)	750 h	Lamp current (nom.)	15.3 A
System description	FastFit	Ignition supply voltage (min.)	198 V
Light Technical		Controls and Dimming	
Colour Code	1	Dimmable	yes
Lamp Luminous Flux 25°C EL (Min)	114750 lm	Mechanical and Housing	
Lamp Luminous Flux 25°C EL (Nom)	127500 lm	Cap base information	PGJX50
Chromaticity coordinate X (nom.)	328	Luminaire Design Requirements	
Chromaticity coordinate Y (nom.)	334	Bulb temperature (max.)	950 °C
Colour Temperature, horizontal (Nom)	5700 K	Pinch temperature (max.)	500 °C
Lamp Luminous Efficacy EM (Nom)	85 lm/W		
Colour Rendering Index at 4 h (Nom)	92		
Colour Rendering Index at 20 h (Nom)	95		

# MSR Gold™ FastFit

## Product Data

Full product code	871869640275700
Order product name	MSR Gold™ 1500/1 FastFit 1CT/4
EAN/UPC – product	8718696402757
Order code	928108905115
Numerator – quantity per pack	1

Numerator – packs per outer box	4
Material no. (12NC)	928108905115
Net weight (piece)	0.133 kg

## Warnings and Safety



## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 1500/1 FastFit 1CT/4	28 mm	6.3 mm	64 mm	66 mm	65 mm	128 mm	50 mm

## MSR GOLD 1500/1 FastFit

## Photometric data



XDPB\_XDMSR\_0002-Spectral power distribution B/W

XDPO\_XDMSR\_0002-Spectral power distribution Colour

