



# MSR Gold™ FastFit

## MSR Gold 1500/1 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


| General Information                |                                  | Color rendering index (CRI) |                               |
|------------------------------------|----------------------------------|-----------------------------|-------------------------------|
| Cap-Base                           | PGJX50                           |                             | 85                            |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] | Arc Length O (Nom)          | 6.3 mm                        |
| Life to 50% Failures (Nom)         | 750 hour(s)                      | Operating and Electrical    |                               |
| Light Technical                    |                                  | Power Consumption           | 1,500.0 W                     |
| Color Code                         | 1                                | Lamp Current (Nom)          | 15.3 A                        |
| Luminous Flux                      | 127,500 lm                       | Controls and Dimming        |                               |
| Chromaticity Coordinate X (Nom)    | 328                              | Dimmable                    | Yes                           |
| Chromaticity Coordinate Y (Nom)    | 334                              | Product Data                |                               |
| Correlated Color Temperature (Nom) | 5700 K                           | Order product name          | MSR Gold 1500/1 FastFit 1CT/4 |
| Luminous Efficacy (rated) (Nom)    | 85 lm/W                          |                             |                               |

# MSR Gold™ FastFit

|                               |                               |
|-------------------------------|-------------------------------|
| Full product name             | MSR Gold 1500/1 FastFit 1CT/4 |
| Full product code             | 871869640275700               |
| Order code                    | 928108905115                  |
| Material Nr. (12NC)           | 928108905115                  |
| Numerator - Quantity Per Pack | 1                             |


|                                 |               |
|---------------------------------|---------------|
| EAN/UPC - Product/Case          | 8718696402757 |
| Numerator - Packs per outer box | 4             |
| EAN/UPC - Case                  | 8718696402764 |

## Dimensional drawing



| Product                       | D (max) | O      | L (min) | L (max) | L     | C (max) | F     |
|-------------------------------|---------|--------|---------|---------|-------|---------|-------|
| MSR Gold 1500/1 FastFit 1CT/4 | 28 mm   | 6.3 mm | 64 mm   | 66 mm   | 65 mm | 128 mm  | 50 mm |

## Photometric data



Spectral Power Distribution Colour - MSR Gold 1500/1 FastFit 1CT/4

