

PHILIPS

Lighting



MASTERColour CDM-R Elite

MASTERColour CDM-R Elite 70W/930 E27 PAR30L 10D

Compact, very high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

Product data

General Information	
Cap base	E27 [E27]
Operating position	UNIVERSAL [Any/Universal]
Life to 5% failures (nom.)	9000 h
Life to 10% failures (nom.)	6500 h
Life to 20% failures (nom.)	12000 h
Life to 50% failures (nom.)	15000 h
Switching cycle	1350X

Light Technical	
Colour code	930 [CCT of 3,000 K]
Beam Angle (Nom)	10 °
Beam angle technical	11 °
Luminous intensity (nom.)	61000 cd
Beam description	Spot
Colour designation	Warm white (WW)
Lumen maintenance 12,000 hours (nom.)	82 %
Lumen maintenance 2,000 hours (nom.)	94 %
Lumen maintenance 4,000 hours (nom.)	90 %
Design mean lumens	3800 lm
Chromaticity coordinate X (nom.)	0.443

Chromaticity coordinate Y (nom.)	0.402
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	70 lm/W
Color rendering index (min.)	89
Color rendering index (nom.)	92
LLMF at end of nominal lifetime (nom.)	80 %
Luminous Flux in 90° Cone (Rated)	4500 lm

Operating and Electrical

Power (Rated) (Nom)	73.2 W
Re-ignition time (min.) (max.)	15 min
Warm-up time to 60% light (nom.)	120 s
Ignition time (max.)	30 s
Voltage (Max)	93 V
Voltage (Min)	79 V
Voltage (Nom)	86 V

Controls and Dimming

Dimmable	no
Run-up time 90% (max.)	3 min

MASTERCoulour CDM-R Elite

Mechanical and Housing

Bulb finish	Clear
-------------	-------

Approval and Application

Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	6.6 mg
Energy Consumption kWh/1000 h	80 kWh

Luminaire Design Requirements


Bulb temperature (max.)	300 °C
Cap base temperature (max.)	200 °C

Product Data

Full product code	871829124186700
-------------------	-----------------

Order product name	MASTERCoulour CDM-R Elite 70W/930 E27 PAR30L 10D
EAN/UPC – product	8718291241867
Order code	24186700
Local Code	70CDM930PAR3010
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	928109300630
Net weight (piece)	0.220 kg
ILCOS Code	MRS/UB-70/930-H-E27-95/125/10


Dimensional drawing




CDM-R Elite 70W/930 E27 PAR30L 10D

Product	D (max)	C (max)
MASTERCoulour CDM-R Elite 70W/930 E27 PAR30L 10D	97 mm	123 mm

Photometric data





LDLD_CDM-R-E_0003-Light distribution diagram



MASTERC colour CDM-R Elite

Lifetime



LDLE_CDM-R-E_930_PAR30L-Life expectancy diagram

