



HORTI

MASTER Agro 400W E40 1SL/12

具有明亮外管的高压钠灯，对植物生长光输出及维护进行了优化

安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	E40 [E40]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	18,000 小时

灯技术	
颜色代码	220 [CCT of 2000K]
色度坐标 X (标称)	0.520
色度坐标 Y (标称)	0.415
相关色温 (标称)	2000 K
光效 (额定) (标称)	130 lm/W
显色指数 (CRI)	20
弧长 O (标称)	83 mm

操作和电气	
功耗	430.0 W
电压 (标称)	128 V
电压 (标称)	128 V


控制和调光	
可调光	否

机械和外壳	
灯泡外观	透明
灯泡外形	T46 [T 46 毫米]

审批和申请	
汞 (Hg) 含量 (标称)	22.0 mg
能耗 kWh/1000 h	473 kWh


产品数据	
订单产品名称	MASTER Agro 400W E40 1SL/12
完整的产品名称	MASTER Agro 400W E40 1SL/12
完整产品代码	871150070750515
订购代码	928144609201
材料编号 (12NC)	928144609201
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500707505
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8711500183019

二维绘图




Product	D (max)	O	L	C (max)	A
MASTER Agro 400W E40 1SL/12	47 mm	83 mm	175 mm	278 mm	205 mm

光度数据




Light Distribution Diagram - MASTER Agro 400W E40 1SL/12

寿命



Life Expectancy Diagram - MASTER Agro 400W E40 1SL/12



Lumen Maintenance Diagram - MASTER Agro 400W E40 1SL/12

