



MASTER SON-T PIA Plus

MASTER SON-T PIA Plus 400W E E40 1SL/12

High Pressure Sodium lamp with clear tubular outer bulb, high output and long reliable lifetime

Product data

General Information			
Cap-Base	E40 [E40]	Lumen Maintenance 20000 h	88 %
Operating Position	UNIVERSAL [Universal]	Lumen Maintenance 5000 h (Min)	90.5 %
Life to 5% Failures (Nom)	20500 h	Lumen Maintenance 5000 h (Nom)	96.5 %
Life To 10% Failures (Nom)	24000 h	Chromaticity Coordinate X (Nom)	525
Life to 20% Failures (Nom)	28000 h	Chromaticity Coordinate Y (Nom)	425
Life to 50% Failures (Nom)	36000 h	Correlated Color Temperature (Nom)	2000 K
ANSI Code HID	-	Luminous Efficacy (rated) (Nom)	137 lm/W
System Description	External Ignitor (E)	Color Rendering Index (Max)	25
LSF 2000 h Rated	100 %	LLMF 2000 h Rated	99 %
LSF 4000 h Rated	99 %	LLMF 4000 h Rated	97 %
LSF 6000 h Rated	99 %	LLMF 6000 h Rated	96 %
LSF 8000 h Rated	99 %	LLMF 8000 h Rated	94 %
LSF 12000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF 16000 h Rated	98 %	LLMF 16000 h Rated	90 %
LSF 20000 h Rated	95 %	LLMF 20000 h Rated	88 %
		Ratio Scotopic/Photopic Lumens	0.60
Light Technical		Operating and Electrical	
Color Code	220 [CCT of 2000K]	Power (Rated) (Nom)	400.0 W
Luminous Flux (Rated) (Nom)	55800 lm	Lamp Current (EM) (Nom)	4.5 A
Lumen Maintenance 2000 h (Min)	95 %	Ignition Supply Voltage (Max)	198 V
Lumen Maintenance 2000 h (Nom)	99 %	Ignition Peak Voltage (Max)	2800 V

MASTER SON-T PIA Plus

Re-ignition Time (Min) (Max)	120 s
Ignition Time (Max)	10 s
Voltage (Max)	115 V
Voltage (Min)	85 V
Voltage (Nom)	100 V

Controls and Dimming

Dimmable	Yes
Run-Up Time 90% (Max)	5 min

Mechanical and Housing

Bulb Finish	Clear
Cap-Base Information	na [-]

Approval and Application

Energy Efficiency Label (EEL)	A++
Mercury (Hg) Content (Nom)	20 mg
Energy Consumption kWh/1000 h	440 kWh

Luminaire Design Requirements


Bulb Temperature (Max)	450 °C
Cap-Base Temperature (Max)	250 °C

Product Data

Full product code	871829166591500
Order product name	MASTER SON-T PIA Plus 400W E E40 1SL/12
EAN/UPC - Product	8718291665915
Order code	928144809295
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928144809295
Net Weight (Piece)	0.177 kg
ILCOS Code	ST-400-H/E-E40

Warnings and Safety

Dimensional drawing




SON-T Plus 400W/220 E40

Product

MASTER SON-T PIA Plus 400W E E40 1SL/12

Photometric data




MASTER SON-T PIA



MASTER SON-T PIA Plus 400W



MASTER SON-T PIA Plus

Photometric data



MASTER SON-T PIA Plus 400W

Lifetime



MASTER SON-T PIA Plus 400 W Lumen Maintenance E40

SON(-T) PIA Plus 150W 250W 400W Life Expectancy Diagram

