



SOX

SOX 135W BY22d T65 1SL/12


Low Pressure Sodium lamp

Product data

General Information	
Cap-Base	BY22d [BY22d]
Operating Position	P20 [Parallel +/-20D or Horizontal(HOR)]
Life to 50% Failures (Nom)	18,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	1800 K
Luminous Efficacy (rated) (Nom)	167 lm/W
Operating and Electrical	
Power Consumption	135.0 W
Lamp Current (Nom)	0.82 A
Voltage (Nom)	164 V
Voltage (Nom)	164 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	T65 [T 65mm]


Approval and Application	
Mercury (Hg) Content (Nom)	0 mg
Energy Consumption kWh/1000 h	155 kWh
Product Data	
Order product name	SOX 135W BY22d T65 1SL/12
Full product name	SOX 135W BY22d T65 1SL/12
Full product code	871150019475615
Order code	928147000018
Material Nr. (12NC)	928147000018
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500194756
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500194763

Dimensional drawing




Product	D (max)	C (max)
SOX 135W BY22d T65 1SL/12	66 mm	775 mm

Lifetime



Life Expectancy Diagram - SOX 135W BY22d T65 1SL/12



Lumen Maintenance Diagram - SOX 135W BY22d T65 1SL/12

