



MASTER SON PIA Plus

MASTER SON PIA Plus 150W/220 E40 1SL/12

High Pressure Sodium lamp with opalized ovoid outer bulb, high output and long reliable lifetime

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


eneral Information		Voltage (Nom)	100 V
Cap-Base	E40	Voltage (Nom)	100 V
Operating Position	UNIVERSAL [Any or Universal (U)]		
Flux measurement reference	Sphere	Controls and Dimming	
Life to 50% Failures (Nom)	36,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	220 [CCT of 2000K]	Bulb Finish	Coated glass
Luminous Flux	16,600 lm	Bulb Shape	BD90
Chromaticity Coordinate X (Nom)	0.535		
Chromaticity Coordinate Y (Nom)	0.42	Approval and Application	
Correlated Color Temperature (Nom)	2000 K	Energy Efficiency Class	F
Luminous Efficacy (rated) (Nom)	107.79 lm/W	Mercury (Hg) Content (Max)	15.1 mg
Color rendering index (CRI)	-	Mercury (Hg) Content (Nom)	15 mg
		Energy Consumption kWh/1000 h	154 kWh
Operating and Electrical		EPREL Registration Number	473387
Power Consumption	154.0 W		

MASTER SON PIA Plus

Product Data	
Order product name	MASTER SON PIA Plus 150W/220 E40 1SL/12
Full product name	MASTER SON PIA Plus 150W/220 E40 1SL/12
Full product code	871150018228915
Order code	18228915
Material Nr. (12NC)	928151409827

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500182289
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500182296


Dimensional drawing




Product	D (max)	C (max)
MASTER SON PIA Plus 150W/220 E40 1SL/12	91 mm	227 mm

Photometric data

Lifetime




Light Distribution Diagram - MASTER SON PIA Plus 150W/220 E40 1SL/12



Spectral Power Distribution Colour - MASTER SON PIA Plus 150W/220 E40 1SL/12

\$ 100 90 90 70 60 50 0 10000
20000
30000
40000 Burning hours

Life Expectancy Diagram - MASTER SON PIA Plus 150W/220 E40 1SL/12



Lumen Maintenance Diagram - MASTER SON PIA Plus 150W/220 E40 1SL/12

MASTER SON PIA Plus



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 16 - data subject to change