



MASTER CityWhite CDO-ET

MASTER CityWh CDO-ET Plus 150W/828 E40

陶瓷複金屬燈室外版本，採用乳色卵形外管

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Warm restart time can be up to 15 minutes; T15 ignitors therefore advised
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	E40 [E40]
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	27,000 h
照明技術	
色碼	828 [CCT of 2800K]
光通量	15,400 lm
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.447
色度坐標 Y (Nom)	0.4
相關色彩溫度 (規範)	2800 K
光效 (額定) (標準)	108 lm/W


演色性指數 (CRI)	85
運轉與電力	
耗電量	143.0 W
電壓 (標稱)	89 V
電壓 (標稱)	89 V
控制與調光	
可調光	是
機械與外罩	
燈泡表層	塗層玻璃
燈泡形狀	BD90 [BD 90mm]

MASTER CityWhite CDO-ET

認證與應用	
節能省電等級	F
汞 (Hg) 含量 (最大)	15.8 mg
汞 (Hg) 含量 (標稱)	15.8 mg
能源消耗 kWh/1000 h	143 kWh
EPREL 註冊碼	473400
產品資料	
下訂產品名稱	MASTER CityWh CDO-ET Plus 150W/828 E40
完整產品名稱	MASTER CityWh CDO-ET Plus 150W/828 E40


完整產品代碼	871829115881300
訂單代碼	928154908835
材質 Nr. (12NC)	928154908835
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718291158813
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8718291158820

二维绘图




Product	D (max)	C (max)
MASTER CityWh CDO-ET Plus 150W/828 E40	91 mm	227 mm

光度数据




Light Distribution Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40




Spectral Power Distribution Colour - MASTER CityWh CDO-ET Plus 150W/828 E40

MASTER CityWhite CDO-ET

壽命



Life Expectancy Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40



Lumen Maintenance Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40

