



HORTI

MASTER GreenPower CG T 600W E40 1SL/12

High Pressure Sodium lamp with clear outer bulb, optimized growthlight output and maintenance

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap base	E40 [E40]
Operating position	UNIVERSAL [Any or Universal (U)]
Life to 50% failures (nom.)	32,000 h
Light Technical	
Colour Code	220 [CCT of 2000K]
Chromaticity Coordinate X (Nom)	0.533
Chromaticity Coordinate Y (Nom)	0.432
Correlated Colour Temperature	2000 K
Luminous efficacy (rated) (nom.)	142.4 lm/W
Colour rendering index (CRI)	26
Arc Length O (Nom)	151 mm
Operating and Electrical	
Power Consumption	618.0 W
Voltage (nom.)	130 V
Voltage (nom.)	130 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T46 [T 46 mm]
Approval and Application	
Mercury (Hg) content (nom.)	30.0 mg
Energy consumption kWh/1,000 hours	680 kWh
Product Data	
Order product name	MASTER GreenPower CG T 600W E40 1SL/12
Full product name	MASTER GreenPower CG T 600W E40 1SL/12
Full EOC	871150020202415
Order code	20202415
Material no. (12 NC)	928158809227
Local order code	6005ONTGP
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500202024


Numerator – packs per outer box	12
EAN/UPC - Case	8711500202031

Dimensional drawing




Product	D (max)	O	L	C (max)	A
MASTER GreenPower CG T 600W E40 1SL/12	47 mm	151 mm	166 mm	279 mm	205 mm

Photometric data




Light Distribution Diagram - MASTER GreenPower CG T 600W E40 1SL/12




Spectral Power Distribution Colour - MASTER GreenPower CG T 600W E40 1SL/12

Lifetime



Life Expectancy Diagram - MASTER GreenPower CG T 600W E40 1SL/12



Lumen Maintenance Diagram - MASTER GreenPower CG T 600W E40 1SL/12

