



Architectural MSD

MSD 700.1CT/3

Architectural MSD – single ended night colours The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent colour rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | Arc Length O (Nom) | |
|------------------------------------|----------------------------------|--------------------------|-----------------|
| Cap-Base | G22 [G22] | 10.0 mm | |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Operating and Electrical | |
| Life to 50% Failures (Nom) | 3,000 hour(s) | Power Consumption | 700 W |
| | | Lamp Current (Nom) | 11 A |
| Light Technical | | Controls and Dimming | |
| Color Code | - [Not Specified] | Dimmable | Yes |
| Luminous Flux | 49,000 lm | Product Data | |
| Chromaticity Coordinate X (Nom) | 317 | Order product name | MSD 700.1CT/3 |
| Chromaticity Coordinate Y (Nom) | 320 | Full product name | MSD 700.1CT/3 |
| Correlated Color Temperature (Nom) | 5900 K | Full product code | 872790091129900 |
| Luminous Efficacy (rated) (Nom) | 70 lm/W | Order code | 928170405114 |
| Color rendering index (CRI) | 75 | | |

Architectural MSD

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 928170405114 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900911299 |
| Numerator - Packs per outer box | 3 |


| | |
|----------------|---------------|
| EAN/UPC - Case | 8727900911305 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F (max) | F | F (min) |
|-----------|---------|------|---------|---------|----|---------|---------|----|---------|
| MSD | 40 mm | 10.0 | 84 mm | 86 mm | 85 | 175 mm | 54 mm | 53 | 52 mm |
| 700.1CT/3 | | mm | | | mm | | | mm | |

Photometric data



Spectral Power Distribution Colour - MSD 700.1CT/3

