



# MSR Gold™ MiniFastFit (Touring/ Stage)

## MSR Gold™ 1000 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	PGJX36 [ PGJX36]	Power (Nom)	1000.0 W
Operating Position	UNIVERSAL [ Any or Universal (U)]	Lamp Current (Nom)	11.4 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	198 V
Life to 50% Failures (Nom)	900 h	Chromaticity Coordinate X (Nom)	0.321
System Description	MiniFastFit	Chromaticity Coordinate Y (Nom)	0.330
Light Technical		Correlated Color Temperature (Nom)	6000 K
Color Code	- [ Not Specified]	Luminous Efficacy (rated) (Nom)	82 lm/W
Luminous Flux (Min)	74000 lm	Color Rendering Index (Nom)	80
Luminous Flux (Nom)	82000 lm		

## MSR Gold™ MiniFastFit (Touring/Stage)

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	PGJX36
Luminaire Design Requirements	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	500 °C
Product Data	
Full product code	871829178508800

Order product name	MSR Gold™ 1000 MiniFastFit 1CT/4
EAN/UPC - Product	8718291785088
Order code	928171405115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928171405115
Net Weight (Piece)	0.055 kg

### Dimensional drawing



MSR GOLD 1000 MiniFastFit

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold™ 1000 MiniFastFit 1CT/4	26 mm	5.5 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

